



## SF Scroll Compressor Offering Overview

Voltage	COM #	Model #	Tonnage	BTU	Shell Diameter	Suction Diameter	Discharge Diameter	Baseplate Footprint
230-3	SFCOM072-23020C	SFCOM072-230-2MSN0C	6	71,780	8.4"	1-1/8"	5/8"	8.5" x 8.5"
	SFCOM084-23020C	SFCOM084-230-2MSN0C	7	87,300	8.4"	1-1/8"	5/8"	8.5" x 8.5"
	SFCOM096-23020C	SFCOM096-230-2MSN0C	8	97,000	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM108-23020C	SFCOM108-230-2MSN0C	9	113,975	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM110-23020A	SFCOM110-230-2MSN0A	9	113,975	10"	1-3/8"	7/8"	8.5" x 12"
	SFCOM120-23020C	SFCOM120-230-2MSN0C	10	121,250	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM125-23020A	SFCOM125-230-2MSN0A	10	121,250	10"	1-3/8"	7/8"	8.5" x 12"
	SFCOM144-23020A	SFCOM144-230-2MSN0A	12.5	148,895	12.5"	1-5/8"	1-1/8"	11" x 12"
	SFCOM168-23020A	SFCOM168-230-2MSN0A	14	168,780	12.5"	1-5/8"	1-1/8"	11" x 12"
	SFCOM180-23020A	SFCOM180-230-2MSN0A	15	179,450	12.5"	1-5/8"	1-1/8"	11" x 12"
460-3	SFCOM072-46020C	SFCOM072-460-2MSN0C	6	71,780	8.4"	1-1/8"	5/8"	8.5" x 8.5"
	SFCOM084-46020C	SFCOM084-460-2MSN0C	7	87,300	8.4"	1-1/8"	5/8"	8.5" x 8.5"
	SFCOM096-46020C	SFCOM096-460-2MSN0C	8	97,000	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM108-46020C	SFCOM108-460-2MSN0C	9	113,975	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM110-46020A	SFCOM110-460-2MSN0A	9	113,975	10"	1-3/8"	7/8"	8.5" x 12"
	SFCOM120-46020C	SFCOM120-460-2MSN0C	10	121,250	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM125-46020A	SFCOM125-460-2MSN0A	10	121,250	10"	1-3/8"	7/8"	8.5" x 12"
	SFCOM144-46020A	SFCOM144-460-2MSN0A	12.5	148,895	12.5"	1-5/8"	1-1/8"	11" x 12"
	SFCOM168-46020A	SFCOM168-460-2MSN0A	14	168,780	12.5"	1-5/8"	1-1/8"	11" x 12"
	SFCOM180-46020A	SFCOM180-460-2MSN0A	15	179,450	12.5"	1-5/8"	1-1/8"	11" x 12"
575-3	SFCOM072-57520C	SFCOM072-575-2MSN0C	6	71,780	8.4"	1-1/8"	5/8"	8.5" x 8.5"
	SFCOM084-57520C	SFCOM084-575-2MSN0C	7	87,300	8.4"	1-1/8"	5/8"	8.5" x 8.5"
	SFCOM096-57520C	SFCOM096-575-2MSN0C	8	97,000	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM108-57520C	SFCOM108-575-2MSN0C	9	113,975	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM110-57520A	SFCOM110-575-2MSN0A	9	113,975	10"	1-3/8"	7/8"	8.5" x 12"
	SFCOM120-57520C	SFCOM120-575-2MSN0C	10	121,250	9"	1-3/8"	7/8"	8.5" x 8.5"
	SFCOM125-57520A	SFCOM125-575-2MSN0A	10	121,250	10"	1-3/8"	7/8"	8.5" x 12"
	SFCOM144-57520A	SFCOM144-575-2MSN0A	12.5	148,895	12.5"	1-5/8"	1-1/8"	11" x 12"
	SFCOM168-57520A	SFCOM168-575-2MSN0A	14	168,780	12.5"	1-5/8"	1-1/8"	11" x 12"
	SFCOM180-57520A	SFCOM180-575-2MSN0A	15	179,450	12.5"	1-5/8"	1-1/8"	11" x 12"