







พัลลภ เตชะสุวรรณ์ Thailand Country General Manager

อีกไม่กี่วัน ก็จะข้ามจากปีเก่า เข้าสู่ปีใหม่ 2022 ซึ่งเป็นปีขาล (เสือ) ผมขอแสดงความ ยินดีกับทุกท่านที่สามารถผ่านพ้นปีที่เรียกได้ ้ว่าเหน็ดเหนื่อยมากปีหนึ่ง แต่ในเรื่องราวไม่ดี ้ที่เกิดขึ้น กลับมีสิ่งที่ดีเกิดขึ้นมากมาย....พวก เราและเด็กๆ เก่งเทคโนโลยีกันมากขึ้นในเวลา อันรวดเร็ว พวกเราดูแลรักษาสุขภาพกันมาก ้ขึ้น และใช้เวลากับครอบครัวมากขึ้นจากการ ้ล็อกดาวน์ พวกเรามีความสุขในการสัญจร บนท้องถนนมากขึ้น เพราะรถติดน้อยลงแบบ ้ที่ไม่เคยเกิดขึ้นมาก่อน มลพิษทางอากาศน้อย ลงจากการที่ใช้รถยนต์น้อยลง เพราะได้ Work From Home

ในปีใหม่นี้ ไม่ว่าทุกท่านจะประสบพบเจอสถาน การณ์ใด ผมขอให้ทุกท่านมีสติในการดำเนิน ้ชีวิต และพยายามหามุมมองด้านบวก เพื่อให้ ้ชีวิตมีความสุขมากขึ้นครับ และผมขอให้ทุก ท่านมี 3 เลือ คือ สุข สำเร็จ สมหวัง กันตลอด ปีครับ

สำหรับ e-Magazine ฉบับนี้ ก็อัดแน่นไปด้วย สาระความรู้ดีๆ เช่นเคย สามารถติดตามอ่าน ได้ในเล่มครับ...สุดท้ายนี้ ผมขอบคุณสำหรับ การสนับสนุนของทุกท่านตลอดปีที่ผ่านมา และฝากทุกท่านติดตามกิจกรรมดีๆ มากมาย ้ที่จะเกิดขึ้นในปี 2022 จาก 'เทรน' ด้วยครับ



& HAPPY NEW YEAR

NOV - DEC 2021: ISSUE 98

- การอัพเกรดเครื่อง 2 ทำน้ำเย็นรุ่น RTHD ด้วยอุปกรณ์ AFD
- IAQ COIL CLEANER AND PRO-ENZYME PAN TABLET
- การเปรียบเทียบการใช้**พลังงาน เชื้อเพลิง**ของ**ระบบทำน้ำร้อน**
- ENGINEERS NEWSLETTER Standard and Codes and Wizards...Oh My!
- มาตรการป้องกัน Covid-19 ในฤดูหนาว และเทศกาลส่งท้ายปี






การอัพเกรดเครื่องทำน้ำเย็นรุ่น RTHD ด้วยอุปกรณ์ AFD (Adaptive Frequency Drive)


เพื่อปรับปรุงประสิทธิภาพการทำงานของเครื่องทำความเย็น และช่วยประหยัดพลังงานมากยิ่งขึ้น

เทคโนโลยีการประหยัดพลังงานของเครื่องทำความเย็น 'เทรน' โดยใช้ AFD (Adaptive Frequency Drive) และระบบควบคุมแบบใหม่ ที่ช่วยปรับปรุงประสิทธิภาพการทำงานของเครื่องทำความเย็น เมื่อมีการใช้งานที่โหลดต่ำลง

ตัวอย่างอุปกรณ์ AFD และหน้าจอระบบควบคุมแบบใหม่




รูปที่ 1 : งานเปลี่ยน AFD โดยเปลี่ยนยกตู้ Starter



รูปที่ 3 : อัพเกรดหน้าจอแบบใหม่ แสดงการแจ้งเตือน เมื่อเครื่อง Alarm ซึ่งง่ายต่อการ monitor



รูปที่ 2: อัพเกรดหน้าจอแบบใหม่ตามรูปแนบ



รูปที่ 4 : อัพเกรดหน้าจอแบบใหม่ แสดงกราฟย้อนหลัง แสดงอุณหภูมิน้ำเข้า-ออกจากเครื่องชิลเลอร์

การติดตั้งชุด AFD กับเครื่องชิลเลอร์รุ่น RTHD จะ ไม่มีการ Modify compressor และไม่มีการ Modify Exchanger จะทำแค่การติดตั้งอุปกรณ์เพิ่มเติม คือ ตู้คอนโทรลใหม่ยกชุด เปลี่ยนถ่ายน้ำมันเครื่อง งานเชื่อมต่อระบบไฟฟ้ากับตู้คอนโทรลใหม่ และ อุปกรณ์เบ็ดเตล็ด ทำให้ติดตั้งง่าย








หลักการทำงานของ AFD (Adaptive Frequency Drive)


การติดตั้ง AFD (Adaptive Frequency Drive) กับเครื่องชิลเลอร์ เพื่อให้เครื่องสามารถทำงานตามโหลดการใช้งานจริง หลักการทำงานของ AFD จะทำงานร่วมกันระหว่าง Drive และ Slide Valve ของเครื่องชิลเลอร์ โดยจะลดกระแสลงมาได้ที่โหลดต่ำถึง 12%RLA (ซึ่งสามารถลดได้ต่ำกว่าเครื่องชิลเลอร์แบบปกติ / Wye Delta) เมื่อเครื่องทำงานที่โหลดต่ำลง Drive จะลดรอบมอเตอร์ลงมาจน ถึง 30 Hz (2,900 rpm to 1,740 rpm) จากนั้น Slide Valve จะทำงานต่อ ทำให้ประสิทธิภาพการทำงานของเครื่องดีขึ้น แม้ในสภาวะ ที่มีโหลดการใช้งานที่ต่ำลง จึงทำให้เกิดการประหยัดพลังงาน

หลังจากติดตั้ง AFD (Adaptive Frequency Drive) ค่าประสิทธิภาพ ของเครื่องซิลเลอร์จะดีขึ้นถึง 25% ตามกราฟรูปล่าง




ข้อดีจากการติดตั้ง AFD (Adaptive Frequency Drive)

1. Energy saving (Part Load)



Graph 1 : Efficiency Comparison




Graph 2: Efficiency Variation





Product Update

2. Lower load capability



โดยปกติการเดินเครื่องชิลเลอร์แบบ Wye Delta ที่ โหลดการใช้งานต่ำ เครื่องชิลเลอร์ จะ Start/Stop บ่อย ส่งผลให้อายุการใช้งานของเครื่องสั้นลง กรณี ที่ติดตั้ง AFD จะช่วยลดการ Start/Stop ของชิลเลอร์ ลงประมาณ 45%


3. Noise reduced at part load

โหลดการใช้งานที่ต่ำลง เสียงของเครื่องชิลเลอร์ แบบ Wye Delta จะดังกว่าที่โหลดการใช้งานที่สูง ดังนั้นการติดตั้ง AFD จะช่วยลดเสียงของเครื่อง ชิลเลอร์ลง 10dB เมื่อโหลดลดลง 50%

4. Lower inrush current


จากตารางด้านล่างแสดงให้เห็นว่ากระแสของเครื่อง ตอนสตาร์ทแบบ Wye Delta กระแสอยู่ที่ 200-275% ถ้าติดตั้ง AFD กระแสตอนสตาร์ทอยู่ที่น้อยกว่า 100% จะเห็นว่าสามารถประหยัดพลังงานตอนเครื่องสตาร์ท ได้เกือบ 3 เท่าของเครื่องชิลเลอร์แบบ Wye Delta

Starter type	Inrush current (% Imax)
Direct in line	600 - 800%
Wye Delta	200 – 275%
Solid State	300 - 500%
AFD	<100%




จากกราฟแสดงกระแสตอน Start ของเครื่องชิลเลอร์ทั้ง สอบแบบ เส้นสีแดงแสดงกระแสตอนสตาร์ท แบบ Wye delta ส่วนเส้นสีเขียวแสดงกระแสตอน Start แบบ AFD

5. Power Factor Correction



การติดตั้ง AFD ทำให้ค่า Power Factor หรือค่าสูญเสีย กำลังงานทางไฟฟ้า คงที่อยู่ที่ 0.95





IAQ COIL CLEANER AND PRO-ENZYME PAN TABLET

หากพูดถึงวิธีการปรับปรุงคุณภาพอากาศ ภายในอาคารแล้ว ยังมีอีกหลายผลิตภัณฑ์ที่ สามารถช่วยในการปรับปรุงคุณภาพอากาศได้ E-MAGAZINE ฉบับที่แล้วได้กล่าวถึงวิธีการใช้ Sensor ชนิดต่างๆ เพื่อปรับปรุงคุณภาพอากาศ ไปแล้ว สำหรับในฉบับส่งท้ายปีนี้ TRANE PARTS & SUPPLIES ขอแนะนำผลิตภัณฑ์ใหม่ล่าสุด ที่เป็นตัวช่วยในการปรับปรุงคุณภาพอากาศ ภายในอาคารได้ นั่นคือ IAQ COIL CLEANER และ PRO-ENZYME PAN TABLET สำหรับคอยล์ เย็นเครื่องปรับอากาศโดยเฉพาะ ซึ่งโดยปกติ แล้ว การใช้งานเครื่องปรับอากาศเป็นเวลานาน ทั้งสิ่งสกปรก ไวรัส แบคทีเรีย เชื้อรา และเมือก ไปโอฟิล์มจะเกาะบริเวณคอยล์เย็น ซึ่งเป็นหนึ่ง ในปัจจัยที่ทำให้อากาศภายในห้องไม่บริสุทธิ์





COIL CLEANER หรือน้ำยาล้างคอยล์สูตร เข้มข้น น้ำยาล้างทำความสะอาดและฆ่าเชื้อโรค สำหรับคอยล์เย็นโดยเฉพาะ ส่วนผสมผลิตจาก Enzyme ชนิดพิเศษ ที่มีคุณสมบัติค่า PH เป็น กลาง ไม่มีส่วนผสมของสารเคมี ไม่เป็นอันตราย ต่อทั้งมนุษย์และสิ่งแวดล้อม ซึ่งส่วนประกอบ ผลิตภัณฑ์ Enzyme จะทำการย่อยสลาย ฆ่าเชื้อ โรคไวรัส แบคทีเรีย เชื้อรา และเมือกไบโอฟิล์ม โดยไม่ทำลายหรือกัดกรอนคอยล์เย็น นอกจาก นี้ผลิตภัณฑ์ยังได้รับการขึ้นทะเบียนเวชภัณฑ์ จากประเทศออสเตรเลีย ARTG No. 371654, (Therapeutic Goods Administration (TGA), Australian Register of Therapeutic Goods (ARTG)) ได้รับรองว่า COIL CLEANER สามารถ ฆ่าเชื้อไวรัส COVID-19 ได้อีกด้วย





Spare Parts

คุณสมบัติโดดเด่น

- √ Enzyme ที่มีค่า PH เป็นกลาง
- √ ฆ่าเชื้อไวรัส COVID-19
- √ ส่วนประกอบ Non Toxic เป็นมิตรกับสิ่งแวดล้อม

ขั้นตอนและวิธีการใช้งาน

- 1. เตรียมน้ำอุ่น อุณหภูมิประมาณ 40°C
- ผสมน้ำยา COIL CLEANER กับน้ำอุ่นใน อัตราส่วน 1:50 ยกตัวอย่าง เครื่องปรับ อากาศขนาด 12,000 BTU/Hr. ใช้ COIL CLEANER ในอัตราส่วน 40 มิลลิลิตร ต่อ น้ำ 2 ลิตร เป็นต้น
- 3. พ่นที่คอยล์ทิ้งไว้ประมาณ 10 นาที
- 4. ล้างออกด้วยน้ำเปล่า








Spare Parts

ก่อนและหลังการใช้ COIL CLEANER




จะเห็นได้ว่าก่อนการใช้ COIL CLEANER ในส่วน คอยล์เย็นจะมีคราบสกปรกทั้งฝุ่น และเชื้อโรคที่ เกาะอยู่บนพื้นผิว Fin คอยล์เป็นปริมาณมาก ซึ่งเป็นผลจากการใช้งานเครื่องปรับอากาศเป็น ระยะเวลานาน ทำให้มีสิ่งสกปรกสะสม ซึ่งหาก เราใช้งานเครื่องปรับอากาศสิ่งสกปรกก็จะปะปน ในอากาศ เมื่อเราสูดอากาศเข้าไปจะเป็นอันตราย ต่อร่างกายได้ หลังจากใช้ COIL CLEANER ทั้ง ในถาดเพาะเชื้อและคอยล์เย็น ตามรูป AFTER จะ ไม่ปรากฏเชื้อราบนถาดเพาะเชื้อทำให้มั่นใจได้ว่า

หลังใช้ COIL CLEANER ลมที่ออกมา จากเครื่องปรับอากาศจะเป็นอากาศ บริสุทธ์ ไม่ปนเปื้อนเชื้อโรคแน่นอน

PRO-ENZYME PAN TABLET อุปกรณ์ป้องกันเมือกในถาดน้ำทั้ง

เป็นอุปกรณ์ที่ยืดอายุการใช้งานถาดน้ำทิ้ง การใช้งานเครื่องปรับอากาศ สาเหตุของการ ที่ทำให้ถาดน้ำทั้งตัน เกิดจากเมือกไบโอฟิล์ม จากการคอนเดนซ์ของน้ำในระบบแอร์ ก่อ เกิดเป็นเมือกไบโอฟิล์มเกาะที่ถาดน้ำทั้ง ซึ่ง PRO-ENZYME PAN TABLET ทำมาจาก Silver Ion และ Enzyme ที่มีคุณสมบัติยับยั้ง การเจริญเติมโตของเมือกจากเชื้อราและเชื้อ แบคทีเรียในถาดน้ำทั้งได้ ไม่มีส่วนประกอบที่ เป็นพิษ สามารถใช้ได้กับเครื่องปรับอากาศ ในทุกอุตสาหกรรม ตัวอุปกรณ์มาในลักษณะ เป็นก้อนสามารถตัดแบ่งการใช้งานได้ โดย PRO-ENZYME PAN TABLET 1 ก้อน (ยังไม่ ตัดแบ่ง) สามารถใช้งานกับเครื่องปรับอากาศ ได้สูงสุดถึง 20 ตัน ซึ่งสามารถใช้งานได้ถึง 6-12 เดือน





Spare Parts


วิธีการใช้งาน

ตัดแบ่ง Pan Tablet ตามขนาดที่ ต้องการโดยที่ไม่ต้องแกะห่อพลาสติก





กด บีบ หรือ ปั้นให้ได้ขนาด ตามพื้นที่ สำหรับพื้นที่วางบริเวณถาดน้ำทิ้ง



3 นำ Pan tablet ที่ปั้นให้เหมาะสม กับพื้นที่วาง ไปวางบริเวณถาด น้ำทิ้ง โดยไม่ต้องแกะห่อพลาสติก ที่ห่อ แผ่นพลาสติกเมื่อโดนน้ำที่ หยดจากคอยล์ จะสลายพร้อมกับ ตัว PRO-ENZYME PAN TABLET เพียงเท่านี้ถาดน้ำทิ้งของเครื่อง ปรับอากาศ จะหมดข้อกังวลใน เรื่องเมือกไบโอฟิล์มที่เป็นสาเหตุ ให้เกิดท่อน้ำทิ้งอุดตันได้









การเปรียบเทียบการใช้**พลังงาน** เชื่อเพลิงของ**ระบบทำน้ำร้อน**เ





ในอดีต การผลิตน้ำร้อนใช้ในอาคาร โรงแรม โรง พยาบาล รีสอร์ต และโรงงาน อุตสาหกรรม โดย ส่วนมากจะใช้หม้อไอน้ำ (Boiler) ร่วมกับเครื่อง แลกเปลี่ยนความร้อน (Heat Exchanger) ซึ่งการ ทำน้ำร้อนประเภทนี้มีค่าใช้จ่ายในด้านพลังงานและ ค่าบำรุงรักษาค่อนข้างสูง และจำเป็นต้องมีช่าง เทคนิคที่มีความรู้ทางด้านหม้อไอน้ำทำการควบ คุมอยู่เสมอ

ในปัจจุบันนี้ แนวโน้มของค่าใช้จ่ายของเชื้อเพลิง สูงขึ้นอย่างรวดเร็ว จึงจำเป็นต้องหาวิธีการทำ น้ำร้อนรูปแบบอื่นๆ หรือการใช้เชื้อเพลิงชนิดต่างๆ เพื่อที่จะลดพลังงานในการผลิตน้ำร้อน เช่น พลัง งานแสงอาทิตย์ (Solar Water Heater) ซึ่งเป็น พลังงานที่ไม่มีค่าใช้จ่ายและไม่มีวันหมด แต่เนื่อง จากมีค่าใช้จ่ายในการติดตั้งอุปกรณ์ค่อนข้างสูง ดังนั้นความนิยมของระบบนี้จึงยังคงมีอยู่ในวง จำกัด

ปัจจุบันมีเทคโนโลยีของเครื่องทำน้ำร้อนแบบหนึ่ง ที่มีประสิทธิภาพสูงและราคารวมทั้งระบบไม่สูงมาก และกำลังเป็นที่นิยม ซึ่งได้แก่ เทคโนโลยีปั๊มความ ร้อน หรือฮีทปั๊ม (Heat Pump) วัฏจักรการทำงาน ของฮีทปั๊ม มีลักษณะการทำงานเหมือนกับระบบ ปรับอากาศ คือ เป็นระบบการทำความเย็นแบบอัด ไอ แต่ข้อแตกต่างระหว่างสองระบบนี้ คือ

ระบบปรับอากาศเลือกใช้ประโยชน์จากด้านความ เย็น ส่วนระบบฮีทปั๊มเลือกใช้ประโยชน์จากด้าน ความร้อนเป็นหลัก และได้ประโยชน์จากด้านความ เย็นเป็นผลพลอยได้ของระบบ โดยฮีทปั๊มมีส่วน ประกอบและหลักการทำงาน ดังนี้

1. คอมเพรสเซอร์ (Compressor)

ทำหน้าที่เพิ่มความดันให้สารทำความเย็นในสถานะ ไอที่อุณหภูมิต่ำให้มีความดันและอุณหภูมิสูงขึ้นจน สามารถควบแน่นได้ที่คอนเดนเซอร์

2. คอนเดนเซอร์ (Condenser)

ทำหน้าที่ระบายความร้อนออกจากสารทำความ เย็นที่ความดันและอุณหภูมิสูง ทำให้สารทำความ เย็นเปลี่ยนสถานะเป็นของเหลวที่ความดันสูง

3. ลิ้นลดความดัน (Expansion Valve)

ทำหน้าที่ลดความดันของสารทำความเย็นเพื่อ ป้อนให้กับเครื่องระเหย

4. เครื่องระเหย (Evaporator)


ทำหน้าที่ดึงอากาศร้อนจากภายนอกเข้ามาแลก เปลี่ยนกับสารทำความเย็นที่ความดันต่ำและ อุณหภูมิต่ำ เพื่อเปลี่ยนสถานะจากของเหลว กลายเป็นไอ **HOSPITAL**







พลังงานความร้อน คือ ผลของความร้อน ทำ ให้สารเกิดการเปลี่ยนแปลง เช่น อุณหภูมิสูงขึ้น หรือมีการเปลี่ยนสถานะสสาร การคำนวณหา ปริมาณความร้อนที่ทำให้สสารเปลี่ยนแปลง อุณหภูมิ สามารถคำนวณได้จากความสัมพันธ์ ระหว่างปริมาณความร้อนที่ทำให้สสารเปลี่ยน แปลงอุณหภูมิมวล และความร้อนจำเพาะการ คำนวณหาพลังงานความร้อนแสดงได้ดังสม การต่อไปนี้



Q คือ ปริมาณความร้อนที่ได้รับหรือสูญเสีย
 ไปมีหน่วยเป็นกิโลจูล (kJ)

m คือ มวลของวัตถุ มีหน่วยเป็นกิโลกรัม (kg)

C_P คือ ความจุความร้อนจำเพาะของวัตถุมี หน่วยเป็นกิโลจูลต่อกิโลกรัมองศาเซลเซียส (kJ/kg°C)

 ΔT คือ อุณหภูมิที่เปลี่ยนไปมีหน่วยเป็นองศา เซลเซียส (°C)

ตัวอย่างการคำนวณหาพลังงานสำหรับระบบ ทำน้ำร้อน


จงคำนวณหาพลังงานความร้อนในการเพิ่ม อุณหภูมิน้ำจาก 30°C ให้มีอุณหภูมิ สูงขึ้นเป็น 60°C โดยน้ำมีปริมาตร ทั้งหมด 5,000 ลิตร

$$Q = 5,000 \text{ kg x } 4.18 \frac{kJ}{\text{kg.C}^{\circ}} \text{ x (60-30) C}^{\circ}$$

Q = 627,000 kJ หรือเท่ากับ 150,000 kcal

Specific heat capacity of water is $4.18 \frac{kJ}{kg.C^{\circ}}$

จากการคำนวณพบว่าในการเพิ่มอุณหภูมิน้ำ จาก 30 องศาเซลเซียส เป็น 60 องศาเซลเซียส ต้องใช้พลังงาน ความร้อน 627,000 kJ หรือ เท่ากับ 150,000 kcal



รูปภาพ แสดงการทำงานเครื่องทำน้ำร้อนแบบปั๊มความร้อน (Heat Pump)

ตารางเปรียบเทียบการใช้พลังงานเชื้อเพลิงของระบบทำน้ำร้อน

รายละเอียด	ระบบทำน้ำร้อน			
2 100-1000	Heat Pump	Electric Water Heater	Diesel Boiler	LPG Boiler
พลังงานที่ใช้ใน การทำความร้อน	150,000 kcal	150,000 kcal	150,000 kcal	150,000 kcal
ค่าพลังงานความร้อน ของเชื้อเพลิง	860 kcal/kW	860 kcal/kW	8,697 kcal/L	11,992 kcal/kg
ประสิทธิภาพของระบบ	380%	95%	85%	85%
ปริมาณความร้อนที่ได้ จากการเผาไหม้อย่าง สมบูรณ์ของเชื้อเพลิง (Available Calorific Value)	3,268 kcal	817 kcal	7,392 kcal	10,193.2 kcal
ปริมาณเชื้อเพลิงที่ใช้	45.89 kW	183.59 kW	20.29 L	14.71 kg
ค่าเชื้อเพลิง	4 Baht/kW	4 Baht/kW	30 Baht/L	22 Baht/kg
ค่าใช้จ่ายเชื้อเพลิง	183.59 Baht	734.39 Baht	608.7 Baht	323.62 Baht
ค่าใช้จ่ายเชื้อเพลิงต่อปี (12 ชั่วโมง/วัน)	804,124	3,216,496	2,666,106	1,417,455
อายุการใช้งาน	10-15 ปี	6-8 ปี	6-10 ปี	6-10 ปี

จากตารางเปรียบเทียบการทำน้ำร้อนโดยใช้เชื้อเพลิงชนิดต่างๆ แสดง ให้เห็นว่าฮีทปั๊มใช้พลังงานน้อยที่สุด เหมาะสมที่จะเลือกใช้ให้เป็นระบบทำน้ำ ร้อน อย่างไรก็ตามต้องพิจารณาความเหมาะสมอื่นๆ ในการที่จะออกแบบ ระบบด้วยนอกเหนือจากพลังงานที่ต้องใช้ เช่น เสถียรภาพของระบบ ปริมาณการทำน้ำร้อน ความปลอดภัยในการใช้งาน ค่าบำรุงรักษาเครื่อง มือและอุปกรณ์ ช่างปฏิบัติการควบคุมระบบ ตลอดจนประสิทธิภาพของ อุปกรณ์ที่ใช้กับเชื้อเพลิงนั้นๆ



Standards and Codes and Wizards...Oh My!

Every three years, the International Code Council® (ICC®) publishes the International Energy Conservation Code® (IECC®) which is the model energy code in many states. The 2021 IECC references 107 other codes and standards from 27 different organizations including 19 from the Air-Conditioning, Heating and Refrigeration Institute (AHRI®) and nine from the ASHRAE® (American Society of Heating, Refrigerating and Air Conditioning Engineers, www. ashrae.org/about).

This newsletter aims to add clarity on United States codes and standards, discuss the typical steps engineers take to review building HVAC system designs against building regulations, and suggest practices and tools that may simplify the internal review process.

How are Codes Influenced by Standards?

Many of us may recall the Saturday morning cartoon Schoolhouse Rock! episode "I'm Just a Bill" which tells the story of how a bill introduced in Congress becomes a law1. Interestingly, some of the cartoon's scenes reflect the development process that standards and codes must follow. Unlike that of a bill, there is no president of HVAC codes that can veto a proposed standard. But there is Federal Government involvement, such as by the Department of Energy (DOE), at key points in the standards and codes development process. So how does a standard become referenced by a building code in a state or municipality and in turn become a job requirement?

The 1999 Engineers Newsletter, titled "The Tortuous Path...From Industry Standard to Local Code", identified three instruments that shape the building regulations enforced by local code authorities: state codes, model codes, and standards ². It also pointed out that states may adjust requirements from a model code or standard to suit their needs. In addition, municipalities may amend the code by ordinance.

In the next section, we'll walk through the step-by-step process used to update ASHRAE Standard 90.1-2013, *Energy Standard for Buildings, Except Low Rise Residential Buildings*³ as an example.


Initiating change

From 2013 to 2016, ASHRAE Standing Standards Project Committee (SSPC) 90.1 received, created, debated, vetted, and voted to publish 120 addenda for inclusion in the Standard. Public review of the proposed addenda generated hundreds of comments either in support of or against the proposed content. The SSPC then met with the commenters in order to resolve their concerns for each addendum. Upon conclusion of the SSPC review process and subsequent public reviews, the ASHRAE Board of Directors (BOD) approved the addenda to the Standard and therefore Standard 90.1-2016 was published in October 2016 4. At this time, unresolved commentors or project committee members who cast negative votes on publication are afforded an appeal to ASHRAE and subsequently the American National Standards Institute (ANSI) if an appeal at ASHRAE was not upheld.

Note: ASHRAE is accredited by ANSI as a developer of American National Standards.







Review process

Following BOD approval, the DOE then initiated a review and determination process of Standard 90.1-2016 as statutorily required by the Energy Policy and Conservation Act (EPCa). The outcome of this review was published in June 2017 in a draft report that stated:

"Commercial buildings meeting the requirements of Standard 90.1-2016 exhibit national savings of approximately (compared to Standard 90.1-2013): 8.2 percent energy cost savings, 7.9 percent source energy savings, and 6.7 percent site energy savings." 5

Given this positive result, the SSPC 90.1 made the recommendation to the ASHRAE Code Interaction Subcommittee (CIS) to submit a code change proposal to the ICC, updating the references to Standard 90.1-2016. After CIS approval, ASHRAE submitted a code change proposal to the ICC that Standard 90.1-2016 be referenced in the latest edition of the code. Public hearings and comment periods followed and ultimately the 2018 IECC was published in August 2017 following the final action hearing. 2018 IECC, Chapter 4, is titled "Commercial Energy Efficiency" and the code provides several commercial building compliance paths with ANSI/ASHRAE/ IES 90.1-2016 listed first (Section C401.2).6 At this point, Standard 90.1-2016 was referenced by a model energy code.

State adoption

The final step in the process is for states to adopt the code. For example, the State of Nevada regulations require adoption of the IECC on a triennial basis following its publication (NRS 701.220 and NAC 701.185 (R153-17AP)) 7,8 which they did in 2018. Given that, Standard 90.1-2016 was required by its reference in 2018 IECC.

At the local level, refinements to the law were made when on August 18, 2018 the city of Las Vegas passed seven pages of amendments to 2018 IECC. These refinements included:

- adding definitions for lighting (i.e. luminaire),
- amending the list of buildings exempted from certain exterior lighting requirements to include casinos, and
- setting specific source energy multipliers used in performance based compliance.9

Recently, Nevada issued a notice of adoption of 2021 IECC, which references 90.1-2019.10 Maine has also made provisions for municipalities to adopt 2021 IECC as a stretch code11, which the cities of Portland and South Portland have done. 12 And, of this writing, over 30 addenda have been published to Standard 90.1-2019. starting the cycle again.

The next section covers resources that can help identify state specific requirements.


Which Code Applies to my **Building Project?**

From an energy standpoint, the IECC and by reference, ASHRAE Standard 90.1, has broad adoption in the US. Figure 1 illustrates the status of state adoption of the energy code as of October 1, 2021. The map takes into account a state's building profile and energy code amendments to reflect the state's "operating energy code", which may be different from the state's adopted energy code. For instance, Wisconsin's current code is 2015 IECC and Standard 90.1-2013, but considering state amendments, it is operating to an energy profile consistent with ASHRAE Standard 90.1-2010. As noted above, Nevada recently adopted 2021 IECC, and Maine has made stretch code provisions which means they are some of the first states to reference ASHRAE 90.1-2019.





Figure 1. State adoption of energy codes of commercial buildings, as of October 1, 2021 13



This Engineering Newsletter is focused on the IECC and 90.1, but many other model codes also reference ASHRAE Standards of interest. Table 1 is taken from information published by the ASHRAE Standards Code Interaction Subcommittee and shows where codes and ASHRAE Standards are related in key building areas.

Table 1. How model codes and ASHRAE standards interact¹⁴

Code-Code Body	Building and Subject Area	Related ASHRAE Standards
IFC—ICC	Fire suppression, mechanical	15
IPC—ICC	Plumbing	188
IMC—ICC	Mechanical	15, 34, 62.1, 170, 180, 188
UMC—IAPMO	Mechanical	15, 34, 62.1, 62.2, 90.1, 111, 128, 170
UPC—IAPMO	Plumbing	90.1, 188
IECC—ICC	Energy	90.1, 90.4
NFPA	Fire suppression, mechanical	15, 34, 55, 62.1, 62.2, 90.1, 90.2





Monitoring state energy code adoption, as well as state legislative moves, can help the engineer keep abreast of current and near-term building code requirements. The DOE maintains an extensive database of state energy code information through the Building Energy Codes Program at www.energycodes.gov. Information on a given state's energy code, amendments, and history are readily available. This represents one of the best resources for US energy code awareness. Additonal code adoption resources are included below.

- BuildingsGuide—State-by-State
 Building Code Resources,
 https://www.buildingsguide.com/blog/
 resources-building-codes-state/
- Insurance Institute for Business & Home Safety[®], https://ibhs.org/public-policy/buildingcodes-by-state/

Engineers can also subscribe to specific standard listservs to gain a sense of code trends. To receive e-mail notification of proposed addenda being issued for public review, you can subscribe to the ASHRAE Listserv at www.ashrae.org/technical-resources/free-resources/listservs.

And, ultimately, participation in the standards development process is the best way to help form the future and understand why changes are made. Visit www.ashrae.org for more information on how to join project committees.

Designing for and Checking Compliance with Standards

So how does an engineer ensure that the design for a specific building complies with the requirements of the energy code? Assuming one is designing in a state that has adopted the IECC (which in turn references ASHRAE 90.1), or that has codified 90.1 directly (e.g., New Jersey) several 90.1 compliance paths are available (Table 2).

During the design process and especially after the compliance path has been chosen, design reviews are important to ensure code compliance. Reviewers should not only be experienced in the pertinent HVAC system, but also be familiar with the permitting jurisdiction. In the words of one design professional:

"During the building design process, engineering firms typically conduct several internal design reviews relying on the technical and code expertise of internal reviewers. Requirements also depend greatly on the building permitting jurisdiction so it's also beneficial that the internal reviewers have code expertise in the permitting municipality. While equipment performance compliance can be checked relatively easily, HVAC system performance compliance is more complicated." 15

To that end, several simulation programs are available to aid the engineer in evaluating the more complicated compliance paths, some of which are noted below.

Compliance Path	Tool
Prescriptive	COM <i>check-Web</i> ™
Performance	eQuest® TRACE3DPlus® HAP DesignBuilder© IESVE© EnergyPlus®

Note that a given simulation program may or may not cover the version of the standard or code required by the jurisdiction, so be sure to check with the simulation program vendor. Also, each of the performance-based simulation programs utilize either public or proprietary calculation engines; public engines include DOE-2™ and EnergyPlus™.

Performance simulation programs are generally required to comply with ASHRAE Standard 140, Method of Test for the Evaluating Building Performance Simulation Software. ¹⁶ Proposed ASHRAE Standard 229P, Protocols for Evaluating Ruleset Implementation in Building Performance Modeling Software ¹⁷ will likely also be required once it is completed.

Table 2. Compliance paths in ASHRAE 90.1

Compliance Path (90.1 sections)	General Description	Partial List of Limits
Simplified approach (6.3)	Packaged equipment meeting minimum efficiency requirements, simple systems with certain features	 Building ≤ 2 stories, < 25,000 ft² Meet requirements of Section 6.3
Prescriptive path (6.5)	Requirements on systems include: Economizers, Simultaneous Heating and Cooling, Air System Design and Control, Hydronic System Design and Control, Heat Rejection Equipment, Energy Recovery, Exhaust Systems, Radiant Heating Systems, Refrigeration Systems	Any building Meet all mandatory requirements of Section 6.4 plus requirements on select systems
Performance path (11, Appendix G)	Whole building analysis with trade- offs to prescriptive paths compared on an energy cost basis (11) or energy performance basis (G)	 Any building Meet all mandatory requirements of Section 6.4 plus design energy cost of proposed building < energy cost budget of baseline building





Performance path example

If a new building is being designed to comply with ASHRAE 90.1 using the Performance Path, performance models are required that predict the energy usage of the "proposed" building as well as the 90.1 minimally compliant "baseline" building. Most software platforms allow the user to model a building in multiple ways for comparison using different alternatives. For this example, both buildings are modeled as separate "alternatives" in the software. Since the proposed building is typically well developed at this point, the task for the engineer is to model the baseline building in order to enable the required energy use and cost comparison.

Requirements for the baseline building, as well as the energy use comparison, are stated in ASHRAE 90.1 Appendix G and include many challenging modelling elements. One such element is reducing the glazing percentages on a building whose proposed alternative has more glazing than the baseline is limited to. Vertical glazing on the baseline is limited to the values defined in Table G3.1.1-1 based on building type. 18 If the proposed building has a higher vertical glazing percentage, it will need to be reduced on the baseline. Different software programs have varying methods for inputting vertical glazing, for example, windows can be input using window dimensions or percent of wall area. This can prove to be a challenge for the modeler due to the multiple steps involved. First, the percentage of vertical glazing for the proposed building needs to be determined. Sometimes this can be gleaned from output reports, otherwise it can be calculated using the window and wall dimension inputs. This process can be lengthy depending upon how the information is presented to the modeler. If the information for each building face is not readily available, then a hand calculation will need to be done for each additional room.

Second, after determining that the proposed building has a higher glazing percentage, the user will need to reduce the glazing percentage on the baseline. This is generally done roomby-room or even window-by-window, depending upon how the glazing dimensions were input. If the glazing was entered as a percentage of wall area, the user can simply reduce the percentage. Otherwise, if the actual dimensions of the windows were entered, those dimensions will need to be correctly reduced for every window in the building. This will need to be done while maintaining the same distribution of glazing for each face of the building (per Table G3.1.5c). 19 If the building model is significant in size, this process can be very timeconsuming!

To address this issue, simulation programs incorporate software automation which can greatly simplify tasks related to standards and code requirements. Based on the example above, software automation allows the user to enter the baseline glazing percentage and the program will automatically adjust the inputs for the windows on the baseline alternative, so that they comply with the required percentage.

Software automation features are sometimes referred to as a "wizard". For those who have toiled through doing it the "old manual way" the "new automated way" seems to defy space and time! Next, we'll discuss the benefits of software automation for codes and standards compliance using TRACE® 3D Plus Standards Wizard as an example.





Overview of TRACE® 3D Plus Standards Wizard

Codes and standards can be very complicated and creating a baseline alternative using a computer simulation program is not always the most straightforward process. Simulation programs are consistently evolving to make the process of keeping up with changing codes and standards more efficient and accurate for the modeler. As an example, TRACE 3D Plus has a Standards Wizard that assists the user in creating an ASHRAE 90.1 baseline by leveraging some automation as well as built in libraries.

Scope

The Standards Wizard in TRACE 3D Plus can assist the modeler in creating an ASHRAE 90.1 baseline for 2007, 2010, and 2013 versions (2016 version coming soon). The user can model the actual proposed building first and then use the software tool to create a 90.1 baseline model to compare to the proposed building.

With inputs from the user, such as building type and climate zone, the tool can copy the proposed building and update it with the appropriate 90.1 construction assemblies and lighting types. Glazing percentage is reduced according to requirements in Appendix G as explained previously. Ventilation is calculated for the proposed building

design and the ventilation rates are applied to the baseline. This allows the proposed and baseline models to use the same rates. Other items, such as weather and utility rates, should be modeled the same on the proposed and baseline buildings. These features are simply copied over by the wizard to the baseline alternative without modification.

Built in libraries are another way to simplify the modeling process. Many tools come with libraries for equipment, construction assemblies, internal loads, etc. that users can reference in their models. Rather than inputting every value referenced by tables throughout 90.1, libraries can come prepopulated with the correct construction U factors and equipment efficiencies as required by the standard.

It is also important to have output available for the user to check compliance with standards. TRACE 3D Plus includes a Leadership in Energy and Environmental Design (LEED*) Report in the format of the Minimum Energy Performance Calculator that is specific to LEED, but the information is also pertinent to 90.1 baseline models.20 There are also input reports available, per the documentation requirement in Standard 90.1 Appendix G, which can assist reviewers in understanding the model inputs without the need for a software license.

What can't be automated

It would be very challenging for a software program to have a single "easy button" to generate a baseline alternative without any additional input from the user. Many sections of the standard come with exceptions, and the tool typically cannot determine which exceptions apply to a particular project. There are also sections of the standard where the user needs to make certain decisions, and those decisions dictate how some part of the baseline should be configured, for example, lighting trade-offs. For this reason, most programs don't have a single button to create an entire baseline, but instead they create some parts automatically while relying on the user to make modifications as needed.





Summary

Many resources exist to aid the engineer's understanding of which codes and standards apply to a given building project. The engineer should check local ordinances in addition to state codes early in the project to ensure the design tracks all compliance requirements. One of the best resources for state codes is www.energycodes.gov.

During the HVAC design process, reviews are important, and reviewers should not only be experienced in the pertinent HVAC system, but also be familiar with the permitting jurisdiction.

Software automation functionality continues to expand and supplement existing project quality assurance practices. Proper use of software automation wizards can significantly reduce the time required for engineering tasks, improve the quality of design submissions, and better ensure design compliance with codes and standards.


And lastly, participating in the US codes and standards process is the best way to form the future of building requirements.

By Rick Heiden and Caitlin Bohnert, Trane. To subscribe or view previous issues of the Engineers Newsletter visit trane.com. Send comments to ENL@trane.com.

References

- "I'm Just a Bill". Schoolhouse Rock! performed by Jack Sheldon, Scholastic Rock, Inc., ABC, 13 March 1976.
- [2] Guckelberger, D. "The Tortuous Path...From Industry Standard to Local Code" *ENEWS*. Volume 28/2. Trane. 1999.
- [3] ANSI/ASHRAE/IES, Standard 90.1-2013, Energy Standard for Buildings Except Low-Rise Residential Buildings. Atlanta, GA: ASHRAE. 2013.
- [4] ANSI/ASHRAE/IES, Standard 90.1-2016, Energy Standard for Buildings Except Low-Rise Residential Buildings. Atlanta, GA: ASHRAE, 2016.
- [5] U.S. Department of Energy, Office of Energy Efficiency & Renewable Energy. Preliminary Energy Savings Analysis ANSI/ASHRAE/IES Standard 90.1-2016. DOE. 2017.
- [6] International Energy Conservation Code (IECC), Chapter 4—Commercial Energy Efficiency. International Code Council, Inc. 2018.
- [7] Nevada Revised Statues. NRS 701-220— Adoption of regulations for energy conservation in buildings; exemptions; applicability and enforcement; procedures for adoption. Nevada. 2014.
- [8] Nevada Energy Codes. NAC 701.185 (R153-17AP)—Approved Legislation of the Director of the Office of Energy. Nevada. 2018.
- [9] Southern Nevada Building Officials. Southern Nevada Amendments to the 2018 International Energy Conservation Code. Las Vegas, NV; S.N.B.O. 2018.
- [10] State of Nevada—Governor's Office of Energy. Notice of Adoption of the 2021 International Energy Conservation Code (IECC). Carson City, NV; 2021.
- [11] State of Maine—Department of Public Safety. Maine Uniform Building and Energy Codes, Chapter 6. IECC International Energy Conservation Code. 2021.
- [12] State of Maine—Department of Energy. City of Portland. https://www.portlandmaine.gov/ CivicAlerts.aspx?AID=5881
- [13] Office of Energy Efficiency & Renewable Energy. Status of State Energy Code Adoption—Commercial. https:// www.energycodes.gov/status/commercial

- [14] ASHRAE, ASHRAE CIS: Code Interaction Subcommittee. Atlanta, GA: ASHRAE. 2021. https://www.ashrae.org/file%20library/ communities/committees/ standards%20committees/cis/cisinformational-flyer.pdf
- [15] Boldt, Jeff. Managing Principal Sr. Mechanical Specialist, IMEG Corp., Middleton, WI. Telephone interview. August 16, 2021.
- [16] ASHRAE Standard 140, Method of Test for the Evaluating Building Performance Simulation Software. Atlanta, GA: ASHRAE. 2019.
- [17] ASHRAE Standard 229P, Protocols for Evaluating Ruleset Implementation in Building Performance Modeling Software. Atlanta, GA: ASHRAE.
- [18] U.S. Green Building Council, LEED Reference Guide for Building Design and Construction (Table G3.1.1-1). Washington D.C. USGBC. 2020.
- [19] U.S. Green Building Council, LEED Reference Guide for Building Design and Construction (Table G3.1.5c). Washington D.C. USGBC. 2020.
- [20] U.S. Green Building Council, Minimum Energy Performance Calculator-ASHRAE 90.1-2010. Washington D.C. USGBC. 2016.





มาตรการป้องกัน Covid-19 ในฤดูหนาว และเทศกาลส่งท้ายปี

เมื่อเข้าสู่ฤดูหนาว อากาศจะเย็นกว่า แห้งกว่า และ นำไปสู่พฤติกรรมที่เพิ่มความเสี่ยงของการแพร่ เชื้อ COVID-19 ในช่วงไม่กี่สัปดาห์ที่ผ่านมา เราได้ เห็นสถานการณ์การแพร่ระบาดทั่วโลกเพิ่มขึ้นอีก ครั้ง ในระลอกที่ 4 ได้เข้าโจมตีประเทศต่างๆ ทั่ว โลกอย่างอย่างรวดเร็ว ซึ่งเป็นสัญญาณเตือนอีก ครั้งสำหรับการป้องกันและควบคุมการแพร่ระบาด ในภูมิภาคของเรา

เมื่อใกล้ถึงเทศกาลคริสต์มาส และวันปีใหม่เราขอ ความร่วมมือทุกท่านให้ปฏิบัติตาม 'มาตรการ ป้องกันการติดเชื้อสำหรับฤดูหนาวและเทศกาล ส่งท้ายปี' เพื่อร่วมเป็นส่วนหนึ่งที่ทำให้ครอบครัว เพื่อน และชุมชนของคุณปลอดภัยสำหรับการรวม ตัวของครอบครัวในวันหยุดยาว

1. คำแนะนำทั่วไปในการป้องกันการแพร่กระจาย เชื้อ COVID-19

- รักษาระยะห่างทางสังคมตั้งแต่ 6 ฟุตขึ้นไปจาก บุคคลภายนอกบ้าน ทุกครั้งที่ทำได้
- สวมหน้ากากอนามัยเมื่ออยู่ในที่สาธารณะ และ เมื่อคุณไม่สามารถรักษาระยะห่างทางสังคมได้
- ล้างมือบ่อยๆ และฆ่าเชื้อพื้นผิวที่สัมผัสบ่อยๆ
- หลีกเลี่ยงไปสถานที่หรือกิจกรรมที่มีคนหนาแน่น
- เมื่อใช้เวลาร่วมกับผู้อื่น การอยู่กลางแจ้งจะ ปลอดภัยกว่าในบ้าน

2. ฉีดวัคซีนป้องกันไข้หวัดใหญ่

วัคซีนป้องกันไข้หวัดใหญ่ไม่สามารถป้องกันการติด เชื้อ COVID-19 ได้ แต่สามารถลดความเสี่ยงของไข้ หวัดใหญ่ การรักษาในโรงพยาบาล และการเสียชีวิตได้ รวมทั้งยังช่วยให้คุณปลอดภัยมากขึ้นเมื่อ COVID-19 กำลังระบาดในฤดูหนาว

3. เตรียมยารักษาอาการไข้หวัดไว้ที่บ้าน

- ในกรณีที่คุณป่วยเป็นหวัดหรือไข้หวัดใหญ่ ให้แน่ใจ ว่าคุณมีสิ่งของพื้นฐานในมือ เพื่อที่คุณจะได้ไม่ต้อง ออกจากบ้านไปซูเปอร์มาร์เก็ตหรือร้านขายยาโดย ไม่จำเป็น เพื่อที่คุณจะมีโอกาสแพร่เชื้อให้ผู้อื่นน้อย ลงด้วย
- สิ่งสำคัญคือ ต้องแน่ใจว่าคุณมีเทอร์โมมิเตอร์ อะเซตามิโนเฟน(Acetaminophen) ชุป และสิ่งพื้น ฐานอื่นๆ ที่จำเป็นสำหรับการเป็นหวัดและไข้หวัด ใหญ่ในกรณีที่คุณป่วย

4. พกหน้ากากอนามัยสำรองไว้เมื่อต้องไปที่สาธารณะ

หากคุณจำเป็นต้องออกนอกบ้านเพื่อทำธุระที่จำเป็น เช่น ไปซื้อของหรือยา ให้นำหน้ากากอนามัยติดตัวไป ด้วย หากคุณจามใส่หน้ากากหรือมีน้ำมูกไหล คุณ สามารถเปลี่ยนใช้อันใหม่ได้อย่างรวดเร็ว และควรนำ ทิชชู่และเจลล้างมือติดตัวไปด้วย

BE HEALTHY, BE CLEAN







CLEAN & DISINFECT







SOCIAL DISTANCE







PICK-UP & DELIVERY













ตรวจสอบให้แน่ใจว่ามีการระบายอากาศที่เหมาะสม เสมอ หากคุณพบปะผู้อื่นนอกบ้าน

- อาจจะเป็นการยากที่จะมีการระบายอากาศที่ดีใน อุณหภูมิที่เย็นในฤดูหนาว แต่สิ่งสำคัญที่สุดคือ การพบปะกับผู้ที่ไม่ได้อาศัยอยู่กับคุณในพื้นที่ที่มี การระบายอากาศเพียงพอเท่านั้น โดยควรอยู่ข้าง นอกอาคาร
- หากคุณกำลังสังสรรค์กับเครือญาติของคุณ หรือ ใครก็ตามที่ไม่ได้อยู่กับคุณ ให้สวมหน้ากาก แม้จะอยู่ ในบ้าน (ของใครก็ตาม)

6. ประโยชน์จากการตรวจหาเชื้อด้วยวิธี Rapid Test

- แม้ว่าจะไม่ใช่วิธีป้องกันการติดเชื้อ แต่การทดสอบ COVID-19 อาจช่วยระบุว่าสมาชิกในครอบครัวที่มี การพบปะกันปลอดภัยจากการติดเชื้อหรือไม่
- มีการทดสอบพื้นฐานสองประเภทที่สามารถตรวจ พบการติดเชื้อ COVID-19 ที่ใช้งานอยู่ : Rapid Antigen Test และ PCR

7. จำกัดการทำกิจกรรม ยกเว้นที่จำเป็นเท่านั้น

ตลอดช่วงการระบาดใหญ่ คำแนะนำทั่วไปคือการ หลีกเลี่ยงการเข้าไปในพื้นที่สาธารณะที่มีผู้คนพลุก พล่าน โดยเฉพาะในอาคาร อย่างไรก็ตาม ในปัจจุบัน การจำกัดกิจกรรมที่ไม่จำเป็นมีความสำคัญมาก กว่าที่เคย โดยเฉพาะอย่างยิ่งหากคุณอยู่ในกลุ่มที่มี ความเสี่ยงสูงชึ่งมีแนวโน้มว่าจะได้รับผลลัพธ์ที่ไม่ดี จากโควิด-19

8. เตรียมพร้อมสำหรับการพบปะ/สนทนาที่ ไม่สบายใจ


ในขณะที่การติดเชื้อยังเพิ่มสูงขึ้นในหลาย ประเทศทางตะวันตก คุณอาจต้องพบปะ พูดคุยทั้งกับเพื่อน และคนแปลกหน้า เช่น หากคุณสงสัยว่าสมาชิกในครอบครัวหรือ เพื่อนไม่ปฏิบัติตามข้อควรระวัง — บางที หลานๆ ของคุณกำลังเล่นนอกบ้านหรือ เพื่อนมารวมตัวกันเพื่อพบปะสังสรรค์ภาย ในห้องปิด — คุณอาจต้องเตือนพวกเขา เพราะคุณไม่ได้อยู่ด้วยกันตลอดเวลา

9. แอคทีฟเมื่อคุณอยู่ที่บ้าน

ฤดูหนาวนี้ คุณต้องพยายามสร้างสรรค์วิธี ที่ทำให้คุณคงความกระฉับกระเฉง ในขณะที่ คุณหลีกเลี่ยงการไปยิมและพื้นที่สาธารณะ เพื่อออกกำลังกาย เพียงแค่ติดตามว่าคุณ ตื่นนอนกี่โมงหรือใช้เครื่องนับก้าวก็เป็นจุด เริ่มต้นที่ดี









Stay safe online.







TECHNOLOGIES

หาวิธีเล็กๆ น้อยๆ ในการต่อสู้กับความเหงา ในช่วงวันหยุดของฤดูหนาวให้สั้นลง

ไม่ว่าคุณจะอายุเท่าไหร่ ใช้เวลาในการเชื่อมต่อ หรือพูดคุยกับผู้อื่นอย่างกระตือรือร้น พูดคุย กับพวกเขาเกี่ยวกับความกังวลและความรู้สึก ของคุณ ศูนย์ควบคุมและป้องกันโรคแห่งสหรัฐ อเมริกา (CDC) ยังแนะนำให้ติดต่อกับองค์กร ในชุมชนหรือองค์กรตามความเชื่อ ไม่ว่าจะทาง ออนไลน์ ผ่านโซเชียลมีเดีย หรือทางโทรศัพท์

ติดต่อกับแพทย์ของคุณเมื่อมีข้อสงสัย หรือ ปัญหาสุขภาพ


- หากคุณเคยเป็น และหายจากโรคต้องสงสัย หรือได้รับการยืนยันการติดเชื้อ COVID-19 สิ่งสำคัญคือต้องระวังผลกระทบระยะยาวที่ อาจเกิดขึ้น
- มีข้อมูลจำนวนมากที่แสดงให้เห็นว่า เมื่อผู้คน ติดเชื้อไข้หวัดใหญ่ พวกเขามีแนวโน้มที่จะเป็น โรคหัวใจและหลอดเลือดเฉียบพลัน เช่น โรค หลอดเลือดสมองหรือหัวใจวาย จากข้อเท็จ จริงที่ว่าโควิด-19 เปรียบเสมือนไข้หวัดใหญ่ แต่เป็นไวรัสที่ร้ายแรงกว่ามาก เรามีเหตุผล ทุกประการที่จะเชื่อว่าผู้คนมักจะมีอาการหัวใจ วาย หรือโรคหลอดเลือดสมองหลังจากนั้น เช่นกัน

'ขอให้เราทำหน้าที่ในส่วนของเราต่อไป ด้วยการมีวินัยในตนเองมากขึ้น เพื่อความปลอดภัยและสุขภาพ ที่ดีในฤดูหนาวนี้ และเพื่อหยุดการแพร่กระจาย เชื้อ COVID-19'















สอบถามข้อมูลเพิ่มเติมได้ที่...

Technician

คุณรณชัย โลพันธ์ศรี โทร. 02 761 1111 ต่อ 8900 e-mail: hrm@trane.com

พัทยา

ข้อมูล ณ เดือนธ.ค. 2564

1





